

PRODUCT-DETAILS

# SR2-DAD-M3

## REC M3 AUTOTST OA-L4M WH



### General Information

Extended Product Type	SR2-DAD-M3
Product ID	7TCA091160R0441
EAN	5415022292428
Catalog Description	REC M3 AUTOTST OA-L4M WH
Long Description	Serenga 2 Anti-Panic Lighting, Recessed Luminaire, M3, 220-240 AC 50Hz, Lamp Type 1 LED 2 W, Lamp Output 203 Lumens, Environment Temperature 5-40 Degrees Celsius, Automatic Self Test, White

### Ordering

EAN	5415022292428
Minimum Order Quantity	1
Customs Tariff Number	9405408440

### Dimensions

Product Net Width	100 mm
Product Net Height	38 mm
Product Net Length	226 mm
Product Net Weight	1.28 lb 580.499 g

### Container Information

Package Level 2 Units	1 piece
Package Level 2 Width	6.5 in 165 mm
Package Level 2 Height	2.44 in 62 mm
Package Level 2 Depth / Length	8.74 in 222 mm

### Additional Information

Battery Type	Industrial
Battery Chemical Composition	Nickel-Metal Hydride
Number of Batteries	1
Product Main Type	SELF CONTAINED LUMINAIRE
Product Name	EMERGENCY LIGHTING
UPC	075114211963

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information	SR2-DAD-M3
Declaration of Conformity - CE	7TKK001142
Instructions and Manuals	7TKK000789

### Classifications

ETIM 6	EC001957 - Emergency luminaire
ETIM 7	EC001957 - Emergency luminaire
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

### Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Emergency Lighting

