

PRODUCT-DETAILS

# SR2-SEM3-BC1

## SFC M3 AUTOTST ESC-MH12M WH



### General Information

Extended Product Type	SR2-SEM3-BC1
Product ID	7TCA091160R0442
EAN	5415022307887
Catalog Description	SFC M3 AUTOTST ESC-MH12M WH
Long Description	Serenga 2 Escape Route, Surface Mount Luminaire, M3, 220-240 AC 50Hz, Lamp Type 1 LED 2 W, Lamp Output 203 Lumens, Environment Temperature 5-40 Degrees Celsius, White

### Ordering

EAN	5415022307887
Minimum Order Quantity	1
Customs Tariff Number	9405408440

### Dimensions

Product Net Width	150 mm
Product Net Height	35 mm
Product Net Length	150 mm
Product Net Weight	1.2 lb 544.218 g

### Container Information

Package Level 2 Units	1 piece
Package Level 2 Width	6.5 in 165 mm
Package Level 2 Height	2.44 in 62 mm
Package Level 2 Depth / Length	8.74 in 222 mm

### Additional Information

Battery Type	Industrial
Battery Chemical Composition	Nickel-Metal Hydride
Number of Batteries	1
Product Main Type	SELF CONTAINED LUMINAIRE
Product Name	EMERGENCY LIGHTING
UPC	075114230582

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information	SR2-SEM3-BC1
Declaration of Conformity - CE	7TKK001142
Instructions and Manuals	7TKK000816

### Classifications

ETIM 6	EC001957 - Emergency luminaire
ETIM 7	EC001957 - Emergency luminaire
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

### Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Emergency Lighting

