

DISCO AMPLIFIER 2 x 480W

AMP600-MKII

Upgraded version of our popular amplifier range. The sturdy 2U case is suitable for 19" rack installation and fitted with handles.

- Recessed volume controls
- Incremented potmeters
- Fan cooling
- Electronic protection against short circuits, dc offset, overload and overheating
- Soft start
- RCA & 6.35mm Jack inputs
- Outputs via Speakon and terminals
- 4 to 8 Ohm impedance
- LED vumeter on every channel

**EAN
CODE**

**5420047137180
17-2151**

SPECIFICATIONS TECHNIQUES

Max. power @ 4 Ohms	2 x 480W
Max. power @ 8 Ohms:	2 x 320W
THD @ 1kHz	1%
Frequency range	20Hz - 20kHz
S/N ratio	>89dB
Channel separation	54dB
Input level	850mV
Input impedance	20kOhms
Power supply	220-240V~ 50/60Hz



LOGISTICS VALUES

Height	15 cm
Width	50 cm
Depth	30 cm
Volume	0.023 m ³
Net weight	5.85 kg
Packaging height	50.5 cm
Packaging width	31.3 cm
Packaging depth	16 cm
Packaging volume	0.025 m ³
Packaging gross weight	6.55 kg
Master carton height	34 cm
Master carton width	51.5 cm
Master carton depth	32 cm
Carton volume	0.056 m ³
Master carton net weight	13.1 kg
Master carton gross weight	14.1 kg
Qty per packaging	1
Qty per master carton	2
Customs code	85185000

