



STAND-ALONE PORTABLE SOUND SYSTEM 12"/30CM WITH USB-MP3, VOX, BLUETOOTH & 2 VHF MICROPHONES

PORT12VHF-MKII

This portable sound system stands out by its exceptional sound quality. Fitted with a built-in rechargeable 4500mA battery, it will run for more than 5 hours. The retractable trolley and polyurethane wheels on ball-bearings allow you to take it with you wherever you go. Wireless VHF microphones (handheld and headset) as well as a remote control ensure optimal versatility and freedom of movement. This extremely versatile system is a precious assistant in many fields: sports associations, street dance, bars, terraces, speakers, business presentations, performing artists and musicians in- and outdoors. Due to the numerous USB / SD / Line / Mic in- and outputs, the unit will cover all your needs.

- MP3, WMA & WAV player via USB & Bluetooth
- 2 VHF mics: Handheld (207.5MHz) & Headset (203.5MHz)
- VHF transmission range of the mics: 25-30m outdoors at free sight; 10-15m indoors
- Fully featured remote control
- VOX function (voice activation)
- Bass & treble EQ
- Mic volume & echo controls
- Music volume control
- Mic & line inputs
- AUX input
- Built-in battery & charger
- Up to 7 hours operating time on battery (depending on the volume level)
- Trolley, handle & wheels for ease of transport
- Tropicalized speaker



LOGISTICS VALUES

Height	56 cm
Width	36 cm
Depth	34.5 cm
Volume	0.07 m ³
Net weight	10.9 kg
Packaging height	63.5 cm
Packaging width	40 cm
Packaging depth	37.8 cm
Packaging volume	96012 m ³
Packaging gross weight	12.6 kg
Qty per packaging	1
nb uvc par palette	15
Customs code	85185000

EAN CODE

5420047137555
17-2602

SPECIFICATIONS TECHNIQUES

RMS / Max. power	350W / 700W
Sensitivity	97dB
Frequency range	40Hz - 20kHz
Power supply	15Vdc 4A
Battery	12V-4.5Ah
Dimensions	360 x 345 x 560mm
Weight	10.9kg

