

# DYMO®



## LabelWriter™ 450

### PROFESSIONAL LABEL PRINTER FOR PC AND MAC®

- Save time - print up to 51 labels per minute\*
- No expensive ink or toner needed - uses thermal printing technology
- Create custom labels from 60+ label styles and layouts
- Prints crystal-clear barcodes, labels and graphics with 600 x 300 dpi resolution
- Eliminate the waste and hassles - print precise quantities and create labels directly from Microsoft® Word, Excel® Outlook®, Google Contacts® with DYMO Connect
- For even more features, download DYMO Connect



### Single Unit Includes:

- LabelWriter 450
- Address Labels Starter Roll - 36x 89mm
- Charging Adapter
- Power Cable
- USB Cable
- Quick Start Guide
- 2 + 1 - Year Limited Warranty\*\*



#### Quick Specs

Unit Dimensions (H x W x L)	134 x 187 x 127 mm
Weight	1.3 kg
Mac®/PC Compatible	Yes via DYMO Connect
Max Label Width	58.42 mm
Resolution	600 x 300 dpi
Printing System	Direct Thermal
Print Speed	51 labels/minute*
Barcodes	Yes
Power Source	Adapter Power Cable
Networking	Print Server Sold Separately
Country of Origin	China

\* 4-line address label

Item Number	Description	Unit	Length (cm)	Width (cm)	Height (cm)	QTY	EAN	Customer Price
S0838810	LabelWriter 450	Unit	14.0	27.0	16.3	1	3501170838815	

\*\* +1 year if registered on the Dymo website

## LW Standard labels

Hassle-free labels for all your mailing, shipping and organizational needs.

Label Type	Description	Code #	Size in mm	Labels/Roll	Rolls/Box	Adhesive	Material
Mailing	Standard Address Labels	S0722370	28 x 89	130	2	Permanent	Paper
	Standard Address Labels	S0722360	28 x 89	130	24	Permanent	Paper
	Standard Address Labels	2093091	28 x 89	130	12	Permanent	Paper
	Assorted Colour labels	S0722380	28 x 89	130	4	Permanent	Paper
	Large Address Labels	S0722400	36 x 89	260	2	Permanent	Paper
	Large Address Labels	S0722390	36 x 89	260	24	Permanent	Paper
	Large Address Labels	S0722410	36 x 89	260	1	Permanent	Transparent Plastic
	Large Return Address Label	S0722520	25 x 54	500	1	Permanent	Paper
Shipping	Shipping / Name badge Labels	S0722430	54 x 101	220	1	Permanent	Paper
	High Capacity Shipping Labels	S0947420	102 x 59	575	2	Permanent	Paper
	Shipping / Name badge Labels	2093092	54 x 101	220	6	Permanent	Paper
	Shipping / Name badge Labels	S0722420	54 x 101	220	12	Permanent	Paper
	Extra Large Shipping Labels	S0904980	104 x 159	220	1	Permanent	Paper
Multi-Purpose	Multi-Purpose Labels	S0722530	13 x 25	1000	1	Removable	Paper
	Square Multi-Purpose Labels	S0929120	25 x 25	750	1	Removable	Paper
	Multi-Purpose Labels	S0722550	19 x 51	500	1	Removable	Paper
	Multi-Purpose Labels	S0722540	32 x 57	1000	1	Removable	Paper
	Large Multi-Purpose Labels	S0722440	54 x 70	320	1	Permanent	Paper
	Large Multi-Purpose Labels	2093094	32 x 57	1000	6	Permanent	Paper
	Large Multi-Purpose Labels	2093095	32 x 57	1000	12	Permanent	Paper
Specialty	Suspension file labels	S0722460	12 x 50	220	1	Permanent	Paper
	LAF Labels small	S0722470	38 x 190	110	1	Permanent	Paper
	LAF Labels large	S0722480	59 x 190	110	1	Permanent	Paper
	Small name badge label	S0722560	41 x 89	300	1	Removable	Paper
	Appointment / name badge cards	S0929100	51 x 89	300	1	Non-adhesive	Paper

## LW Durable Labels

Tear-resistant, coated polypropylene labels with extra-strength adhesive that withstand abrasion, common cleaners, and a wide range of temperatures-ideal for shelving, storage, and signage.



Water



Solvents



Oil



Textured Surfaces



Temperature  
-18°C to 50°C

Label Type	Description	Code #	Size in mm	Labels/Roll	Rolls/Box	Adhesive	Material
Durable	LW Durable Labels	1933081	25 x 89	350	1	Permanent	Coated Polypropylene
	LW Durable Labels	1976411	25 x 54	160	1	Permanent	Coated Polypropylene
	LW Durable Labels	1933088	59 x 102	300	1	Permanent	Coated Polypropylene
	LW Durable Labels	1933085	19 x 64	450	2	Permanent	Coated Polypropylene
	LW Durable Labels	1933083	25 x 25	850	2	Permanent	Coated Polypropylene
	LW Durable Labels	1933084	57 x 32	800	1	Permanent	Coated Polypropylene
	LW Durable Labels	1933087	59 x 190	170	1	Permanent	Coated Polypropylene
	LW Durable Labels	1933086	104 x 159	200	1	Permanent	Coated Polypropylene

The DYMO high quality labels are made in Belgium