
CONTROL UNITS... Type T


Dimensions


Push Buttons






* Dimensions over live terminals






Type TRD

Selector Switch Operators







	Dimension A	Dimension B
Standard Knob Gloved Hand	40	27
Knob	51	44


Dimensions when using Contact blocks

For all type KA, except single throw KA.G




* Dimensions over live terminals





Single throw KA.G

Minimum spacings



Drilling Template for Mounting All Units

31 diameter hole may be cut with a knockout punch. Locating pin hole 3.5, as shown above horizontal (or top of button). Guard may be rotated to other positions by drilling locating pin holes in proper location.



Dimensions in mm