

PRODUCT-DETAILS

93-B

M20 LOCKNUT BLACK PACK QTY 100



Product image
not available

General Information

Extended Product Type	93-B
Product ID	7TCA296220R0480
EAN	5016947057712
Catalog Description	M20 LOCKNUT BLACK PACK QTY 100
Long Description	Locknut for Cable Gland with M20 Thread, Nylon, Black

Ordering

EAN	5016947057712
Customs Tariff Number	3926909990

Dimensions

Product Net Weight	.005 lb 2.268 g
--------------------	--------------------

Container Information

Package Level 1 Units	100 piece
Package Level 2 Units	3000 piece
Package Level 2 Width	1 in 25 mm
Package Level 2 Height	1 in

	25 mm
Package Level 2 Depth / Length	1 in 25 mm

Additional Information

Application	To Be Used with Non-Metallic Fittings When Securing Into Knockouts
Brand / Label	Adaptaflex
Color	Black
Construction Material	Nylon
Number of Batteries	0
Product Name	plastic locknut
Product Type	Locknut with Metric Threads
Thread Size	M20
Thread Standard	Metric
UPC	786210255774

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	93-B
Declaration of Conformity - CE	9AKK107492A9618
Instructions and Manuals	93-B

Classifications

ETIM 6	EC000940 - Locknut for cable screw gland
ETIM 7	EC000940 - Locknut for cable screw gland
UNSPSC	31161716
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	2849 >> Locknuts

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems



Product image
not available