

CR1232

QUAD TV/FM DAB/SAT PLATE



Instinct™
WIRING ACCESSORIES

CONSTRUCTION

| | |
|------------------|----------------------|
| Product Category | Wiring Accessory |
| Product Group | Data & Communication |
| Product Type | Monoblock Plate |
| Shape | Square Plate |
| Material | Urea Formaldehyde |
| Finish | Moulded |
| Mounting Type | Flush/Surface |

POWER

| | |
|---------------------------|----------------|
| Current | Not Applicable |
| Current Type | Not Applicable |
| Frequency | Not Applicable |
| Input Voltage | Not Applicable |
| Switched Poles | Not Applicable |
| Number of Rocker Switches | 0 |
| Number of Ways | Not Applicable |
| Fuse Rating | Not Applicable |

AESTHETICS

| | |
|-------------------------------|--|
| Plate Gang / Module Size | 1 Gang |
| Plate Colour | White |
| Rocker Colour | Not Applicable |
| Light Reflectance Value (LRV) | 74 |
| Printing Text/Type | TV, FM/DAB SAT1 SAT2, Laser Printed |
| Status Indicator | N |
| Switched Outlets | N |
| Part M Compliance | Y |
| Anti Microbial Properties | Y |
| Key Features & Benefits | Curved Slimline Plate Monoblock Communication Solution Indelible Laser Marking |

TERMINAL

| | |
|---|----------------|
| L & N Terminal Capacity as per BS Standard | Not Applicable |
| Earth Terminal Capacity as per BS Standard | Not Applicable |
| Number of Earth Terminals | 0 |
| Cable Strip Length | Not Applicable |
| Screwdriver Type Required | Not Applicable |
| Torque requirement as per BS Standard L&N | Not Applicable |
| Torque requirement as per BS Standard Earth | Not Applicable |

LOCATION

| | |
|---|----------------|
| Max Ambient Operating Temp as per BS Req. | Not Applicable |
| Min Ambient Operating Temp as per BS Req. | Not Applicable |
| Max Altitude as per BS Requirement | 2000m |
| IP Rating | Not Applicable |

DIMENSIONAL / FIXING

| | |
|-------------------------------|--------------|
| Height | 86mm |
| Width | 86mm |
| Depth Overall | 39mm |
| Depth Interior only | 27mm |
| Gross Weight | 0.13kg |
| Minimum Back Box Depth | 35mm |
| Suggested Back Box Depth | 35mm |
| Fixing Centres | 60.3mm |
| Minimum Access Top | 100cm |
| Minimum Access Bottom | 100cm |
| Minimum Access Left | 100cm |
| Minimum Access Right | 100cm |
| Minimum Access Front | 100cm |
| Minimum Access Rear | 100cm |
| Flush Mounting Metal Box | SB615 (35mm) |
| Flush Mounting Dry Lining Box | SB619 (35mm) |
| Surface Mounting Box | 9041 (44mm) |

STANDARDS


| | |
|--------------------------|--|
| British Standard/s | BS 5733, ANSI/SCTE 02:2006, IEC 61169-2:2007, BS EN 60728-11:2005 |
| Other Markings/Standards | CE |

PACKAGING

| | |
|------------------|---|
| Inner Carton Qty | 8 |
| Customer MOQ | 8 |

SUSTAINABILITY

| | |
|------------------------|---|
| URL to technology list | https://www.crabtreecommercial.co.uk/ |
|------------------------|---|



Electrium Sales Limited
A Siemens Company
Tel: +44 (0) 1543 438310
Fax: +44 (0) 1543 000000
Email: crabtree.technical@electrium.co.uk
www.electrium.co.uk

Although every effort has been made to ensure accuracy in the compilation of the technical detail within this publication, specifications and performance data are constantly changing. Latest details can be obtained from Crabtree.



Crabtree