

由Autodesk教育版产品制作

USB 3.1 C/M Nickel plated

P1



6.65±0.15




USB3.1 (#32*1P+D+AL+MY)*4C+#32*4C+#32*1P+#26*1C+#28*1C+AB BLACK PVC Jacket OD4.0MM

BLACK PVC Jacket

Black ABS shell

B11 B10 B8 A5 B5 B3 B2 VBUS



A11 A10 A8 A7 A6 A3 A2 GND



Black ABS shell

HDMI A/F
Nickel plated

P2



- 1. 100% OPEN SHORT MIS WIRE TEST
- 2. CONTACT RESISTANCE:5 OHM MAX
- 3. INSULATION RESISTANCE:5M OHM MIN
- 4. HI-POT TEST:DC 300V/10ms
- 5. PASS 3840*2160P 30HZ EST

CONSUMER ITEM	LENGTH (mm)
PSG3315	200±10

				DESCRIPTION	FINISHED PRODUCT'S FIGURE	SCALE	FIT	UNITS: MM	1RD ANGLE
				MODEL NO.		△			
APPROVED	CHECKED	DRAWING	DESIGNED	DRAWING NO.	256-044	△			
				FINISHING		△	2020/6/23		A1
				MATERIAL		SYM	DATE		REVISION