

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301510022](#)  
**Status:** **Active**  
**Overview:** [Heavy-Duty Industrial Wiring Devices](#)  
**Description:** Super-Safeway Adapter NEMA 5-20 Receptacle - Female End 20A/125V, P&S Pins Plug - Male End, 20A/125V

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA      LR6837

**General**

Product Family      Wiring Devices  
Series      [130151](#)  
IP Rating      N/A  
NEMA Configuration      NEMA 5-20  
Overview      [Heavy-Duty Industrial Wiring Devices](#)  
Product Name      Super-Safeway  
Receptacle Type      N/A  
Specialty      N/A  
Type      Adapter  
UPC      78678875023

**Physical**

Flange      No  
Flip Lid      No  
Gender      Male-Female  
Length      N/A  
Locking Blade      No  
Net Weight      0.174/kg  
Poles      2-pole/3-wire

**Electrical**

Cord Type      N/A  
Current - Maximum per Contact      60.0A  
GFCI      No  
Lighted Connector      No  
Voltage - Maximum      125V

**Material Info**

Engineering Number      1733



**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Relevant**

**REACH SVHC**

Not Relevant

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Relevant

**China RoHS**

**Search Parts in this Series**

[130151](#) Series