

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301530280](#)
Status: **Active**
Overview: Ground Fault Circuit Interrupter (GFCI) Products
Description: Super-Safeway In-Line GFCI, Portable, Single Phase, Manual Reset, Flying Leads (Primary) and Watertite Extreme NEMA 5-20 Connector (Secondary), 20A, 120V, 12/3 SJE00W Cord, 9.14m (30') Cord Length

Documents:

[Drawing \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E66308

General

Product Family	Power Distribution
Series	130153
Enclosure Rating	NEMA 4X
GFCI Reset	Manual
Mounting Style	Portable
Open Neutral Relay	Yes
Overview	Ground Fault Circuit Interrupter (GFCI) Products
Product Name	Super-Safeway
Receptacle Type	Single
Type	GFCI Industrial Duty, Single Phase
UPC	78172562124

Physical

Cord Diameter	10.92mm (.430")
Cord Grip Body Size	N/A
Cord Length	9.14m (30.0')
Feed-Thru	Yes
Flip Lid	No
Material - Housing	Nylon
Number of Receptacles	1
Packaging Type	Carton

Electrical

Cord Type	12/3 SJE00W
Current - Maximum per Contact	20.0A
GFCI	Yes-In-line
Ground Continuity Monitor	No
NEMA Configuration	NEMA 5-20
Voltage - Maximum	120V

Material Info

Engineering Number 20052-0PM30



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130153 Series](#)