

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301530279](#)

**Status:** **Active**

**Overview:** Ground Fault Circuit Interrupter (GFCI) Products

**Description:** Super-Safeway In-Line GFCI Portable, Single Phase, Manual Reset, Flying Leads (Primary) and Watertite Extreme NEMA 5-20 Y-Splice (Secondary), 20A, 120V, 12/3 SOOW Cord, 6.10m (20') Cord Length

**Documents:**

[Drawing \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E66308

**General**

Product Family	Power Distribution
Series	<a href="#">130153</a>
Enclosure Rating	NEMA 4X
GFCI Reset	Manual
Mounting Style	Portable
Open Neutral Relay	Yes
Overview	<u>Ground Fault Circuit Interrupter (GFCI) Products</u>
Product Name	Super-Safeway
Receptacle Type	Y-Splice
Type	GFCI Industrial Duty, Single Phase
UPC	78172561324

**Physical**

Cord Diameter	15.11mm (.595")
Cord Grip Body Size	N/A
Cord Length	6.10m (20.0')
Feed-Thru	Yes
Flip Lid	No
Material - Housing	Nylon
Net Weight	3103.479/g
Number of Receptacles	2 - Y-Splice
Packaging Type	Carton

**Electrical**

Cord Type	12/3 SOOW
Current - Maximum per Contact	20.0A
GFCI	Yes-In-line
Ground Continuity Monitor	No
NEMA Configuration	NEMA 5-20
Voltage - Maximum	120V, 240V

**Material Info**

Engineering Number 20052-Y-20MH



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130153 Series](#)