

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301530278](#)
Status: **Active**
Overview: Ground Fault Circuit Interrupter (GFCI) Products
Description: Super-Safeway In-Line GFCI, Portable, Single Phase, Manual Reset, Flying Leads (Primary) and Watertite Extreme NEMA 5-20 Connector (Secondary), 20A, 120V, 12/3 SJEOOW Cord, 5.18m (17') Cord Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Datasheet \(PDF\)](#)

Agency Certification

UL E66308

General

Product Family Power Distribution
 Series [130153](#)
 Enclosure Rating NEMA 4X
 GFCI Reset Manual
 Mounting Style Portable
 Open Neutral Relay Yes
 Overview [Ground Fault Circuit Interrupter \(GFCI\) Products](#)
 Product Name Super-Safeway
 Receptacle Type Single
 Type GFCI Industrial Duty, Single Phase
 UPC 78172560541

Physical

Cord Diameter 10.92mm (.430")
 Cord Grip Body Size N/A
 Cord Length 5.18m (17.0')
 Feed-Thru Yes
 Flip Lid No
 Material - Housing Nylon
 Net Weight 1737.710/g
 Number of Receptacles 1
 Packaging Type Carton

Electrical

Cord Type 12/3 SJEOOW
 Current - Maximum per Contact 20.0A
 GFCI Yes-In-line
 Ground Continuity Monitor No
 NEMA Configuration NEMA 5-20
 Voltage - Maximum 120V

Material Info

Engineering Number 20052-0PM18



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130153 Series](#)