

PRODUCT-DETAILS

CP-D24/2.5

CP-D24/2.5 priOn Power Supply, 24 V DC, 2.5 A, MDRC



General Information

Extended Product Type	CP-D24/2.5
Product ID	2CDG120037R0011
EAN	4016779697897
Catalog Description	CP-D24/2.5 priOn Power Supply, 24 V DC, 2.5 A, MDRC
Long Description	For Busch-priOn Buscoppler. The MDRC device supplies a regulated output voltage of 24 V DC with a maximum output current of 2.5A

Ordering

EAN	4016779697897
Customs Tariff Number	85044090
Minimum Order Quantity	1 piece

Dimensions

Product Net Depth / Length	57.5 mm
Product Net Height	91 mm
Product Net Width	71 mm
Product Net Weight	0.252 kg

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 EAN	4016779697897
Package Level 1 Depth / Length	85 mm
Package Level 1 Height	132 mm
Package Level 1 Width	85 mm
Package Level 1 Gross Weight	0.311 kg

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	2CDC114056D0202 2CDC114058B0201
Instructions and Manuals	9AKK2017-107080
Declaration of Conformity - CE	9AKK2017-107078
RoHS Information	9AKK2017-107082

Environmental

RoHS Status	Following EU Directive 2002/95/EC August 18, 2005 and amendment
-------------	---

Classifications

ETIM 5	EC002540 - DC-power supply
ETIM 6	EC002540 - DC-power supply
ETIM 7	EC002540 - DC-power supply
eClass	7.0 27049002
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
IDEA Granular Category Code (IGCC)	4130 >> DC-power supply

Categories

Low Voltage Products and Systems → Control Products → Power Supplies

Low Voltage Products and Systems → Home and Building Automation → KNX → Power Supply → Auxiliary Power Supplies

Low Voltage Products and Systems → Home and Building Automation → KNX → User Operation - Busch-priOn → Base Frames and Accessories

