


03 038799

Circular connectors with threaded joint M16 acc. to IEC 61076-2-106, IP40/IP67/IP68



Protecting cap, IP68, for sockets, without chain

03 038799



Environmental conditions

Temperature range -40 °C/+85 °C

Materials

Cap PC

Mechanical data

Tightening torque connector 1-3 Nm

Tightening torque nut 1-3 Nm

Protection class IP68¹

¹ according to IEC DIN EN 60529, only in locked condition with an appropriate counterpart; IPX8 requirements under agreement between manufacturer and user

Associated products

Accessories

☞ 030398	☞ 0304	☞ 0304-1
☞ 0304-2	☞ 0305	☞ 0305-1
☞ 0305-1 U	☞ 0305-2	☞ 0306
☞ 0306-1	☞ 0306-2	☞ 0307
☞ 0307-1	☞ 0307-2	☞ 030798-1
☞ 030798-2	☞ 030799-2	☞ 0308
☞ 0308-1	☞ 0308-2	☞ 0321
☞ 0322	☞ 0322-1	☞ 032200
☞ 0360	☞ 036000	☞ 0362
☞ 036297	☞ 0363	☞ KFR
☞ KfV	☞ KGR	☞ KGV
☞ KV	☞ KV ...-8	☞ WKV

03

038799

Designation	Pole Number	PU (Pieces)	MDQ (Pieces)
038799	-	50	500

Packaging:

in a cardboard box