



# CorePro LEDspot MV

## CorePro LEDspot 4-35W GU10 830 36D DIM

CorePro LEDspots are a perfect fit for spot lighting and deliver warm halogen-like light. They are compatible with most existing fixtures with a GU10 or E27 base and are designed as a retrofit replacement for halogen or incandescent spots. CorePro LEDspots deliver significant energy savings and minimize maintenance cost.

### Product data

General Information	
Cap-Base	GU10 [ GU10]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	50000X
Technical Type	4-35W
Light Technical	
Color Code	830 [ CCT of 3000K]
Beam Angle (Nom)	36 °
Luminous Flux (Nom)	260 lm
Luminous Intensity (Nom)	540 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	65.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	260 lm
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	4 W


Lamp Current (Nom)	19 mA
Wattage Equivalent	35 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	65 °C
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy Efficiency Label (EEL)	A+
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	4 kWh
Product Data	
Full product code	871869672135300
Order product name	CorePro LEDspot 4-35W GU10 830 36D DIM
EAN/UPC - Product	8718696721353
Order code	929001363902

# CorePro LEDspot MV

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001363902

Net Weight (Piece)	0.038 kg
--------------------	----------


## Dimensional drawing




GU10 230V 4-35W 260lm 36D 3000K GU10 D

Product	D	C
CorePro LEDspot 4-35W GU10 830 36D DIM	50 mm	54 mm


## Photometric data



LEDspot,PAR38 11W 900lm 3000K





Classic LEDspotMV 35W GU10 830 36D



CorePro LEDspotMV 35W GU10 830 36D CLA

# CorePro LEDspot MV

## Lifetime



CLA LEDspotMV 50W GU10 827 36D ND

CLA LEDspotMV 50W GU10 827 36D ND

