

## Current clamp 400A AC

### Characteristics

- Current measurement up to 400A AC
- Range of 40A for low current measurement: 10mA resolution
- Jaws opening: 25mm
- Voltage measurement up to 600V AC and DC
- Resistance measurement
- Continuity measurement with buzzer
- Automatic power-off
- Hold function
- LCD display 4000 points
- Safety: 600V - CAT III

Specifications	BK 312C
<b>AC current</b>	
Bandwith	50Hz to 400Hz
Ranges	40A - 400A
Resolution	0,01A
Accuracy	±(1.9% + 3dgt)
<b>AC Voltage</b>	
Bandwith	50Hz to 400Hz
Ranges	400V - 600V
Resolution	100mV - 1V
Accuracy	±(1.2% + 3dgt)
<b>DC voltage</b>	
Ranges	400V - 600V
Resolution	100mV - 1V
Accuracy	±(1.0% + 3dgt)
Impedance	3,5MΩ // 100pF
<b>Resistance</b>	
Range	400Ω
Resolution	1Ω
Accuracy	±(1.9% + 3dgt)
Continuity	with buzzer for R<25Ω
<b>Spécifications générales</b>	
Digital display	LCD screen
Display	3 digits 3/4, 3999 points
Jaws Opening	25mm
Measurement rate	2 measurement/s
Automatic power-off	after 10 minutes
Operating Temperature	0°C to 40°C
Storage temperature	-10°C to 60°C
Protection	Electronic on all scaling
Safety	600V - CAT III
Power supply	2 batteries 1,5V AAA
Power life	50h
Dimensions	203 x 75 x 32mm
Weight	270g
Warranty	1 year



**Supplied with:** bag, test leads with touch point, user's guide, batteries.

FT BK312C A 00- Specifications can be updated without notice

# Sefram



32, rue Edouard Martel - BP55- 42009 - St Etienne - cedex 2  
 Tél. +33 (0) 4.77.59.01.01  
 Fax. +33 (0) 4.77.57.23.23  
 Web : [www.sefram.com](http://www.sefram.com) - e-mail : [sales@sefram.com](mailto:sales@sefram.com)

Follow us on :



### For assistance and ordering

