



# Wi-Fi 6/6E TRIPLE BAND EMBEDDED ANTENNA

Part Numbers: 2344657-1, 2344657-2

2344657-3, 2344657-4

2344657-5, 2344657-6

2344657-7, 2344657-8


## **FEATURES & BENEFITS**

- Wi-Fi 6, also including Wi-Fi 6E new 6GHz band, Bluetooth, ZigBee
- Adhesive backing on FPC simplifies mounting within the device
- Omnidirectional coverage
- No matching components required
- Ground-plane independent design
- Different cable length and connector options available


### **SPECIFICATIONS**

Frequency Range (MHz)	2400-2500	5150-5850	5925-7125		
VSWR	< 2.7:1	< 2.1:1	<2.1:1		
Average Efficiency	61%	72%	66%		
Peak Gain	1.1dBi	4.9dBi	5.3dBi		
Average Gain	-2.5dB	-1.1dB	-1.4dB		
Power Handling	10 Watt cw				
Feed Point Impedance	50 ohms unbalanced				
Polarization	Linear				
Size	35 mm x 8.0 mm x 0.2 mm				
Weight	< 0.8 g				
Mounting	Adhesive Tape				
Mating Connectors	MHF-type receptacle (TE PN 2337019-1), MHF4-type receptacle (TE PN: 2334884-1)				
Operating Temperature	-40 to +85°C				
Storage Temperature	-40 to +85°C				
Hazardous Materials	A certificate of conformance is available from the product page on TE website.				

## **RF DATA**




## Efficiency




Data measured in free space and on plastic device enclosure

### RADIATION PATTERN




Data measured in free space and on plastic device enclosure

## **KEEP OUT AREA**



#### **NOTES**


- 1. Antenna designed to be mounted on plastic cover.
- 2. Area in blue indicates Keep Out Area
- 3. Contact TE if keep out zone cannot be guaranteed.



Dimension: mm

Diagrams is not into scale

## **DIMENSIONS**




### **MATING COMPONENTS**


	1	1			
2344657-1	50	1.97	MHF-TYPE PLUG	RECEPTACLE (TE PN: 2337019-1)	
2344657-2	100	3.94	MHF-TYPE PLUG	RECEPTACLE (TE PN: 2337019-1)	
2344657-3	150	5.91	MHF-TYPE PLUG	RECEPTACLE (TE PN: 2337019-1)	
2344657-4	200	7.87	MHF-TYPE PLUG	RECEPTACLE (TE PN: 2337019-1)	
2344657-5	50	1.97	MHF4-TYPE PLUG	RECEPTACLE (TE PN: 2334884-1)	
2344657-6	100	3.94	MHF4-TYPE PLUG	RECEPTACLE (TE PN: 2334884-1)	
2344657-7	150	5.91	MHF4-TYPE PLUG	RECEPTACLE (TE PN: 2334884-1)	
2344657-8	200	7.87	MHF4-TYPE PLUG	RECEPTACLE (TE PN: 2334884-1)	and the state of t
PART	MM	INCH	CONNECTOR TYPE	PART NUMBER	IMAGE
NUMBER	NUMBER CABLE LENGTH ("A") (ON CABL		(ON CABLE)	MATING COMPONE	NTS

### **PACKAGING**





200PCS/BAG DESICCANT:1PCS/BAG



#### TE TECHNICAL SUPPORT CENTER

USA: +1 (800) 522-6752 Canada: +1 (905) 475-6222 Mexico: +52 (0) 55-1106-0800 Latin/S. America: +54 (0) 11-4733-2200 +49 (0) 6251-133-1999 Germany: UK: +44 (0) 800-267666 France: +33 (0) 1-3420-8686 +31 (0) 73-6246-999 Netherlands: China: +86 (0) 400-820-6015

For phone numbers in other countries, go to te.com/support-center

#### te.com

TE Connectivity, TE Connectivity (logo) are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective names.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2020 TE Connectivity Ltd. family of companies All Rights Reserved.

07/2020

