

# Speed Punch™ Set ISO 16 - 40



- ▶ Up to 3-times faster than conventional punching tools
- Easy and quick handling as the screwing and unscrewing of the counter nut is not required
- Compatible with all Greenlee hand-operated and battery powered hydraulic tools
- ▶ No greasing of the draw stud required

### **Suitable for**

Mild steel (St37), plastic and aluminium up to 3.5 mm

### **Operation**

Hydraulic

### **Predrilling**

 Draw stud 9.5 mm dia., pilot drill 9.7 mm dia. 50360183 draw stud 19.0 mm dia., pilot drill 20.5 mm dia. 50344030

## **Scope of supply**

- Complete system including draw stud, cramp, punch and die incl. plastic case

Item	Part No.
Speed Punch <sup>™</sup> punch set ISO 16/20/25/32/40	52055439SET
Scope of supply	Part No.
Punch and die ISO 16 (16.2 mm)	52055431
Punch and die ISO 20 (20.4 mm)	52055432
Punch and die ISO 25 (25.4 mm)	52055434
Punch and die ISO 32 (32.5 mm)	52055435
Punch and die ISO 40 (40.5 mm)	52055436
Speed Lock and draw stud 9.5 mm for ISO 16/20/25 and PG 16	52055439
Speed Lock and draw stud 19.0 mm for ISO 32/40/50/63	52055440
Plastic case	KKSPIS016B63
Accessories	Part No.
Plastic case	KKSPIS016B63