

Product Specifications

SRH1540 Premium Studio Headphones

Overview

Building on over 85 years of audio experience, the SRH1540 Premium Studio Headphones deliver superior audio performance, comfort and durability to listeners of all kinds - professional engineers, musicians and audiophiles. The SRH1540 utilizes 40 mm neodymium drivers for an expansive soundstage with clear, extended highs and warm bass. Developed with aluminum alloy and carbon fiber construction, the lightweight and durable design also features Alcantara® ear pads for maximum sound isolation and comfort.

Features

- 40 mm neodymium drivers deliver superior acoustic performance for an expansive soundstage with clear, extended highs and warm bass
- Closed-back, circumaural design rests comfortably over the ears and reduces background noise
- Lightweight construction featuring aircraft-grade aluminum alloy yoke and carbon fiber cap for enhanced durability
- Steel driver frame with vented center pole piece improves linearity and eliminates internal resonance for consistent performance at all listening levels
- Ergonomic dual-frame, padded headband is lightweight and fully adjustable for hours of listening comfort
- Oxygen-free copper cable (OFC) with Kevlar® reinforced jacket for superior performance and durability
- Dual-exit cables with gold-plated MMCX connectors provide secure connection and detachability for easy storage or replacement
- Replaceable ear pads made with Alcantara® and low density, slow recovery foam for exceptional comfort
- Additional cable, replacement ear pads and zippered storage case included for years of listening enjoyment
- Legendary Shure durability to withstand the rigors of everyday use



Available Models

SRH1540	Includes a threaded 1/4" (6.3 mm) gold-plated adapter, zippered hard storage case, two detachable cables, and additional pair of Alcantara® ear pads
----------------	--

Specifications

Type	Closed-back, circumaural
Transducer Type	Dynamic, Neodymium magnet
Driver Size	40 mm
Frequency Range	5 Hz - 25 kHz
Sensitivity (@ 1 kHz)	99 dB/mW
Impedance (@ 1 kHz)	46 Ohms
Maximum Input Power	1000 mW
Connector	Gold-plated 3.5 mm (1/8") stereo mini jack plug with 6.35 mm (1/4") threaded adapter
Cable Length/Type	6 ft (1.83 m) dual-exit, detachable oxygen-free copper
Removable Ear pads	Yes
Collapsible	No
Net Weight (without cable)	10.1 oz (286 g)

Accessories and Replacement Parts

Replacement Alcantara® Ear Pads	HPAEC1540
Threaded 1/4" Adapter	HPAQ1
Zippered, Hard Storage Case	HPACC3
Replacement Dual-Exit Cable Assembly	HPASCA3

