



TECHNICAL INFORMATION

Input Power:	AC:220-240V, 50Hz
Unit Color:	White
Body Type:	Aluminium + Glass
Dimmable:	No
Rated Load:	Max 40W
Dimension:	170x170x840mm

CEILING LAMPS

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 7073 - 940

[View more details](#)



COMPATIBLE WITH
E27 BULBS

*Bulbs are not included



**TRADITIONAL
GARDEN LAMPS**

**ALUMINIUM &
GLASS BODY**



FEATURES

- Traditional garden lamps designed to meet modern day requirements
- Strong and sturdy Aluminium + Glass body
- Offering IP44 Ingress protection
- Compatible with E27 holder type (Fitting only - light not included)
- Suitable for gardens, patio, pathways etc.
- Recommended daily usage: 10 - 12 hours *Exceeding recommended daily usage will void warranty

CE/EMC

CE/LVD



PACKAGING

Gross Weight (Kgs):	1.08
Unit CBM:	0.00558
Dimension:	170x170x840mm

MASTER BOX PACKAGING

Box Qty:	10
Qty Per Pallet:	240
Length (Box) mm:	180
Width (Box) mm:	160
Height (Box) mm:	200

LISTING DETAILS

Commodity Code:	9405109890
EanCode:	3800157616263