



TECHNICAL INFORMATION

Watts:	1.5
Lumens:	220
Unit Color:	Black
Body Type:	ABS + PC
LED Chip Type:	SMD
Operation Temperature:	-25°C to +50°C
Dimmable:	No
Beam Angle:	90°
Color:	4000K
Dimension:	144.5x96x79mm
Detection Range:	2-6m
Battery Type:	3.7V Lithium Battery 1200mAh
Charging Time:	6-7 Hours Sunlight Charging
Working Time:	Maximum 24 Hours
No. Of Led:	14



FEATURES

- Uses mono-crystalline solar panels for efficient photo voltaic conversion and lengthy lifespan
- PIR sensor for automatic switching on and switching off
- Easy to install, requires no wiring
- Robust and durable ABS plastic body
- Dust, heat and water resistant
- Renewable energy source: Solar powered
- Available range: 1.5W to 6.8W
- Suitable for gardens, pathways, garages etc.

CE/EMC

CE/LVD



SOLAR WALL LIGHTS

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 8277 - 1541 938

[View more details](#)



ABS + PC body

SMD LED'S

flexible & efficient

PACKAGING

Gross Weight (Kgs):	0.266
Unit CBM:	0.00288
Dimension:	144.5x96x79mm

MASTER BOX PACKAGING

Box Qty:	20
Qty Per Pallet:	760
Length (Box) mm:	240
Width (Box) mm:	150
Height (Box) mm:	85

LISTING DETAILS

Commodity Code:	9405403990
EanCode:	3800157627948