



TECHNICAL INFORMATION

| | |
|------------------------|----------------|
| Lumens: | 550 |
| Input Power: | DC:3.2V |
| Long Life: | 20,000 Hours |
| Unit Color: | Black |
| Body Type: | Aluminium |
| LED Chip Type: | SMD |
| CRI: | >70 |
| Operation Temperature: | -20°C to +45°C |
| Dimmable: | No |
| Beam Angle: | 120° |
| Color: | 4000K |
| Dimension: | 205x50x170mm |
| Battery Type: | 5000mAh |
| Charging Time: | 4 Hours |
| Working Time: | 8 Hours |
| Solar Panel: | 12W |



FEATURES

- Solar Powered Floodlight - Zero electricity cost.
- Designed with Remote control, Auto and timer function.
- Flexible installation, designed with solar panel with 5 meter wire length
- Perfectly built for outdoor with Ingress protection of IP65
- Suitable for Pathways, Garden, Patio and similar outdoor environment

CE/EMC

CE/LVD



SOLAR FLOODLIGHTS

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 8573 - 938

[View more details](#)



REMOTE CONTROL AUTO AND TIMER FUNCTION



PACKAGING

| | |
|---------------------|--------------|
| Gross Weight (Kgs): | 1.898 |
| Unit CBM: | 0.0063 |
| Dimension: | 205x50x170mm |

MASTER BOX PACKAGING

| | |
|------------------|-----|
| Box Qty: | 8 |
| Qty Per Pallet: | 240 |
| Length (Box) mm: | 90 |
| Width (Box) mm: | 200 |
| Height (Box) mm: | 350 |

LISTING DETAILS

| | |
|-----------------|---------------|
| Commodity Code: | 9405403990 |
| EanCode: | 3800157645584 |