



TECHNICAL INFORMATION

Lumens:	1050
Input Power:	DC:6V
Long Life:	20,000 Hours
Unit Color:	Black
LED Chip Type:	SMD
Operation Temperature:	-20°C to +45°C
Dimmable:	No
Color:	6000K
Battery Type:	10000mAh
Solar Panel:	16W



FEATURES

- Solar Powered Floodlight - Zero electricity cost.
- Designed with Remote control, Auto and timer function.
- Flexible installation, designed with solar panel with 5 meter wire length
- Perfectly built for outdoor with Ingress protection of IP65
- Suitable for Pathways, Garden, Patio and similar outdoor environment

CE/EMC

CE/LVD



SOLAR FLOODLIGHTS

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 94008 - 938

[View more details](#)



ZERO ELECTRICITY COST

**FULLY SOLAR
POWERED**

**EASY INSTALLATION
NO WIRING**

**5
METER
WIRE**

PACKAGING

Gross Weight (Kgs): 2.871

Unit CBM: 0.0108

MASTER BOX PACKAGING

Box Qty: 6

Qty Per Pallet: 150

Length (Box) mm: 100

Width (Box) mm: 300

Height (Box) mm: 360

LISTING DETAILS

EanCode: 3800157645751