



## TECHNICAL INFORMATION

Watts:	5
Lumens:	400
Input Power:	AC:200-240V, 50/60Hz
Long Life:	20,000 Hours
Unit Color:	White+Satin Nickel
Body Type:	Plastic + Ferrum
PF:	>0.5
LED Chip Type:	SMD
CRI:	>80
Operation Temperature:	-20°C to +45°C
Dimmable:	No
Beam Angle:	110°
Color:	3000K
Equivalence Watts:	35
Dimension:	120x99mm



## FEATURES

- Pack of 3 GU10 Spotlights designed with fittings
- Includes GU10 holder along with quick connector for easy wiring
- Stable SMD technology for better reliability and longer lifespan
- Reliable IC Power Driver
- Up to 80% in energy savings when compared to standard Halogen spotlights
- Excellent heat radiation efficiency
- Easy to install recessed installation
- Suitable for hotels, bars, commercial, residential lighting, exhibition stands etc.
- Note: Suitable and Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

CE/EMC

CE/LVD



## GU10 3PC PACK FITTING | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

*One brand, endless solutions..*

SKU: 8884 - 1263 1688

[View more details](#)



## PACKAGING

Gross Weight (Kgs): 0.0029575  
Unit CBM: 0.0029575  
Dimension: 120x99mm

## MASTER BOX PACKAGING

Box Qty: 20  
Qty Per Pallet: 400  
Length (Box) mm: 130  
Width (Box) mm: 350  
Height (Box) mm: 65

## LISTING DETAILS

Commodity Code: 9405403990  
EanCode: 3800157650069