



TECHNICAL INFORMATION

Watts:	150
Lumens:	18000
Input Power:	AC:95-265V, 50/60Hz
Long Life:	30,000 Hours
Unit Color:	Black
Body Type:	Die-Cast Aluminium
PF:	>0.9
LED Chip Type:	SMD-Samsung Chip
CRI:	>70
Dimmable:	Yes
Beam Angle:	120°
Color:	6400K
Dimension:	Ø340x171mm
lumens per watt:	120
LED Chip Solution:	9V 100mA

PRO UFO SERIES MW 120°

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 559 - 935 938

[View more details](#)



IP65
RATING



5 YEAR
WARRANTY



IK 07



Your Reliable Power Partner



1-10V
DIMMABLE



120
Lumen/W

FEATURES

- Powerful LED light source with lumen efficiency of 120 LM/W
- Radiator integrated cooling fins for efficient heat dissipation
- Fitted with high efficiency Samsung LED Chips that offer up to 85% in energy savings
- Designed with Meanwell driver
- Longevity and efficient lumen maintenance
- Suitable for industrial usage, warehouses, supermarkets, workshops, factories, warehouses, highways, toll stations, gas stations, malls, exhibition halls, and stadiums
- Recommended daily usage: 10 - 12 hours *Exceeding recommended daily usage will void warranty

PACKAGING

Gross Weight (Kgs): 3.491
Unit CBM: 0.025857
Dimension: Ø340x171mm

MASTER BOX PACKAGING

Box Qty: 2
Qty Per Pallet: 48
Length (Box) mm: 170
Width (Box) mm: 390
Height (Box) mm: 390

LISTING DETAILS

Commodity Code: 9405403990
EanCode: 3800157632843

CE/EMC

CE/LVD

