

Product information

35 31 115

Electronics Pliers

DIN ISO 9655



- Precision pliers for fine assembly work, e.g. in electronics and fine mechanics
- For gripping, holding and bending
- Sturdy, zero backlash box joint
- Smooth ground gripping surfaces
- Edges carefully deburred
- Low-friction double spring for gentle and even opening
- The polish or mirror polish (only finish 2) together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Round, pointed jaws
- Ball bearing chrome steel



General	
Article No.	35 31 115
EAN	4003773016762
Head	mirror polished
Handles	with non-slip plastic coating
weight	61 g
Dimensions	115 x 50 x 33 mm
Standard	DIN ISO 9655

Technische Attribute	
Style	3
	22.5 mm
	6.5 mm
	2.0 mm
	1.0 mm
Head width	11.0 mm

Classification	
eCl@ss 5.1.4	21040301
proficl@ss 6.0	EAA840c015
UNSPSC 13.1	27112149

technical change and errors excepted

