

Product information

98 37 12

- For metric and imperial hexagonal head screws
- Basic tool chrome plated
- Chrome Vanadium steel

Hexagon Socket for hexagonal screws

With internal square 3/8"

IEC 60900 DIN EN 60900



⚡ 1000 V ⚡

General	
Article No.	98 37 12
EAN	4003773020608
weight	33 g
Dimensions	44 x 78 x 33 mm
Standard	DIN EN 60900 IEC 60900

Technische Attribute	
Width across flats S	12 mm
dia. of effective tool side d max.	21.2 mm
Square drive	38

Classification	
eCl@ss 5.1.4	21040218
ETIM 5.0	EC002203
ETIM 6.0	EC002203
proficl@ss 6.0	AAA805c006
UNSPSC 13.1	27111700

technical change and errors excepted