




Product Code: PM3BKM

Description: 250V 20A 3 Pole Male Locking Panel Mount Outlet



General Information

Rating	20A 250V~
Colour	Black
Materials	Body: Polyamide (PA6/6 V0) Contacts: Brass Silver Plated Clamping Spring: HT Treated Steel
Number Of Poles	3
Terminal Type	Push-fit (2 cables per terminal)
Metal Panel Thickness	0.5mm - 1.2mm
Panel Cutout	33mm (+0.10mm) x 15.6mm (+0.10mm)
Terminal Cable Size	0.5mm² Min. - 2.5mm² Max.
Termination Lengths	Stripped: 10mm
Ferrule / Bootlace	0.5mm² Min. - 1.5mm² Max.
Temperature Rating	100°C
Ingress Protection	IP20 (IP40 When Plugged In) FSSR3BKF
Locking Facility	Yes

Additional Information Installation couplers are only intended for connection and disconnection without load. This installation coupler is not suitable for installation in readily accessible areas.

Standards EN61535: 2008 +A1: 2013,
EN 60335-1

