

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2153431103](#)
Status: **Active**
Overview: Off-the-Shelf Pre-Crimped Leads
Description: Pre-Crimped Lead Mini-Fit Jr. Male-to-Pigtail, Tin (Sn) Plating, 225.00mm Length, 20 AWG, Black

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Datasheet \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	215343
Application	Power, Wire-to-Wire
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Mini-Fit Jr.-to-Pigtail
Overview	<u>Off-the-Shelf Pre-Crimped Leads</u>
Product Name	Mini-Fit Jr.
UPC	193264560110

Physical

Cable Length	225.00mm
Circuits (Loaded)	1
Color - Resin	Black
Gender	Male-Pigtail
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	2.943/g
Packaging Type	Bag
Single Ended	Yes
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.80-3.10mm
Wire Size AWG	20
Wire/Cable Type	UL 1015

Electrical

Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

Material Info

Reference - Drawing Numbers

Sales Drawing	2153431101-000
---------------	----------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[215343](#) Series

Use With

Mini-Fit Jr. Plug Housing [5559](#)
Mini-Fit
BMI Plug Housing [42475](#)