

EDIFIER®

S2000MKIII

2.0 Powered Bookshelf Speakers

Edifier enters the realm of music production with the S2000MKIII active monitor speakers, designed for home recording & mixing. For maximum clarity, the S2000MKIII speakers are tri-amped with 130 watts, featuring 5 ½” aluminium diaphragm drivers and a set of planar tweeters for great acoustic range.

The additional bluetooth capability lets you connect to your various audio sources remotely. It is designed with top quality components and rugged construction for complete performance.



Features

- Bluetooth V5.0 with Qualcomm® aptX™ HD decoding
- 5 ½” Aluminium diaphragm drivers for ultimate bass response
- Patent-pending planar diaphragm tweeters that adapt to a wide range of acoustic conditions
- High efficiency Class-D digital power amplification
- Electronic crossovers and dynamic control based on dual advanced DSP chips
- Supports digital audio signal with sample rate up to 24BIT/192KHZ
- Listening presets: Monitor, Dynamic, Classical, and Vocal
- OLED LCD screen displays source/volume/sound effects modes for more convenient use
- PVC side panels with matte black finish
- IR remote control



Specifications

Power output	: L/R (treble): 15W+15W RMS L/R (mid-range bass): 50W + 50W RMS
Signal to noise ratio	: ≥90dB(A)
Noise level	: ≤25dB(A)
Input sensitivity	: Line 1 input: 800±50mV   Line 2 input: 600±50mV Bluetooth input: 450±50mFFs Optical/Coaxial input: 350±50mFFs
Frequency response	: 45Hz~40KHz
EAN code	: 6923520268276

Package Info

Dimension	198 x 276 x 342mm,(WxHxD),17.14kg
Inner Carton	505 x350 x 412 mm,(LxWxH), 19.39kg (gross weight)
Master Carton	520 x 365 x 433 mm,(LxWxH), 20.5kg (gross weight)
PCS/CTN	1