



# 886E

Product no.: 886E

Side cutter - tapered head




The jaws of the cutter have straight edges and taper to a point. This head shape allows access to difficult to reach areas but reduces the cutting capacity in comparison to the same size oval head cutter.



source images

## The Perfect Cut - Strong, sharp and precise, every time

The Weller Erem Series 800 Maxi is a range of maxi-sized precision cutters for general cutting applications in electronics to cut large wire diameters. The cutters are made from high grade tool steel with cutting edges hardened to 63-65HRc. The precision cutters have a nonreflecting surface, are ESD safe and resharpenable.

		Type	Type of Cut	Cutting Capacity
<b>Series 800 Maxi &amp; 2800</b>				mm 0,03 0,1 0,2 0,3 0,4 0,5 0,6 0,7 0,8 0,9 1,0 1,1 1,2 1,3 1,4 1,5 1,6 1,7 1,8 1,9 2,0 Inch .0001 .003 .007 .011 .015 .019 .023 .027 .031 .035 .039 .043 .047 .051 .055 .059 .062 .066 .070 .074 .078
	<b>812N 2812N</b>		<b>Semi Flush</b>	
	<b>822N 2822N</b>		<b>Flush</b>	
	<b>886E 2886E</b>		<b>Flush</b>	
	<b>884E 2884E</b>		<b>Flush</b>	





**Technical Data**

Length mm	120
Length of cutting edges mm	15
Head width mm	13.5
Head thickness mm	7.2
Head length mm	21
Max. cutting capability – hard wire mm	---
Weight in oz	2.998
Length of cutting edges Inches	0.590
Head width Inches	0.531
Head thickness Inches	0.284
Head length Inches	0.827
ESD-safe	on
Cut	Flush
Max. cutting capability – medium hardness mm	Ø 1,0
Max. cutting capability – copper wire mm	Ø 1,8
Length inches	4.724
Weight in g	85
Erem applications	---