







2482E

Product no.: 2482E

Tip cutter - angled narrow head.



The angled head allows precise cuts at different working angles.




Suitable for working on printed-circuit boards, component connections, can be used in both 90° and 180° applications

source images

The Perfect Cut - Strong, sharp and precise, every time

The Weller Erem Series 2400 Magic Sense is a range of medium-sized precision cutters that combines robustness, visibility and accessibility. A large variety of head shapes for precision work in hard-to-reach areas. The optimized ergonomic shape of the Series 2400 MagicSense prevents hand fatigue. These cutters are manufactured from improved induction-hardened cutting edges up to 64 – 65 HRc for an extremely long service life. The cutting edges are made from special tool steel. The precision cutters have a nonreflecting surface, are ESD safe and resharpenable.















Length mm	135
Length of cutting edges mm	6
Head width mm	11
Head thickness mm	6
Head length mm	26
Max. cutting capability – hard wire mm	
Weight in oz	2.677
Length of cutting edges Inches	0.236
Head width Inches	0.433
Head thickness Inches	0.236
Head length Inches	1.024
ESD-safe	on
Cut	Flush
Max. cutting capability – medium hardness mm	Ø 0,6
Max. cutting capability – copper wire mm	Ø 1,2
Length inches	5.315
Weight in g	75.9
Erem applications	Microelectronic