



Description: Two ventilation fan versions: DFN01 for mounting to a surface from below, DFN02 for mounting on top of a surface, with flow always pointing upwards. Extra contact provided for thermostat connection.

Voltage: 220-240 VAC.

Air circulation: 160 m³/h.

Power of the fan: 19 Watt.

Pack quantity: 1 set with finger guards and mounting screws.

Note: For easy connection use wiring kit DFN61.

Description	Item no.
Top mounting	DFN02
	DFN61

When ventilator holes are not used they can be closed with DFC closing plates.