



Jig Saw

Item No.: 4321145

Ident No.: 11016

Bar Code: 4006825619737

The Einhell TC-JS 80/1 jigsaw is the ideal tool for performing cutting work in the workshed, garage and the DIY enthusiast's cellar. With its 550 W it is remarkably powerful. It effortlessly tackles wood, plastic or steel. The four-setting pendulum action enables exact and fast cuts to be performed. The jigsaw allows a cutting depth of up to 80 millimeters for wood, 20 millimeters for plastic and up to 10 millimeters for steel. Softgrip surfaces make the Einhell TC-JS 80/1 jigsaw pleasant to work with. The soleplate can be swiveled, allowing miter cuts at angles of up to 45 degrees. The dust extractor keeps the work area clean. The saw blade can be changed quickly and effortlessly without the need for any tools.

Features

- Easy changing of the saw blades without any tools
- Electronic speed control for ideal speed for the work material
- 4-setting pendulum action for exact and fast cuts
- Soleplate can be swiveled to allow miter cuts up to 45°
- Dust extraction keeps the work area clean
- Large Softgrip surfaces for comfortable operation

Technical Data

220-240 V | 50/60 Hz - Mains supply

- Power 550 W

- Number of strokes 1000 - 3000 min^-1

- Stroke height 20 mm - Cutting depth in wood 80 mm 20 mm - Cutting depth in plastic - Cutting depth in steel 10 mm - Max. bevel cuts 45°

Logistic Data

- Product weight 1.85 kg - Gross weight single packaging 2.4 kg

- Dimensions single packaging 282 x 86 x 212 mm

- Pieces per export carton 6 Pieces - Gross weight export carton 14.2 kg

436 x 265 x 296 mm - Dimensions export carton - Container quantity (20"/40"/40"HC) 4734 | 9996 | 0















