

STI MUGGER STOPPER® PLUS



STI-12006

PRODUCT OVERVIEW

Mugger Stopper Plus helps stop mugger attacks or harassment two ways: with an ear piercing 120 dB alarm or with an attention grabbing strobe light.

This two-way action also makes it more effective in summoning aid in case of an injury or fall. In addition, the built-in light can be used as a flashlight to help you find your keys or the keyhole on those dark, moonless nights.

HOW IT WORKS

To activate the Mugger Stopper Plus alarm and strobe light, simply pull out the plug on top of the unit. To turn on the built-in flashlight, slide the button on the side of the unit up.

IMPORTANT: The Mugger Stopper Plus alarm is extremely loud. Never place the unit close to your ears. To test alarm, direct the unit away from you at arms length and pull out pin on top of unit.

KEY FEATURES

General Information

- Strobe light makes it even more effective in summoning aid in case of injury or fall.
- Handy built-in flashlight to find keys, etc.
- Activate by pulling pin out on top of unit.
- Carry in pocket or purse.
- With belt clip, can be worn on hip to resemble cell phone or pager.
- Makes an ideal gift or stocking stuffer.
- One year warranty.

Construction

- Shock resistant and lightweight.

Electronics

- 120 dB, 9 VDC battery operated alarm (battery not included).

STI Mugger Stopper® Plus


Dimensions and Technical Information

MODEL AVAILABLE


STI-12006 Mugger Stopper Plus with built-in flashlight

WARRANTY

One year warranty from the date of original purchase.



To activate both Mugger Stopper Plus alarm and strobe light, simply pull out pin on top of unit.



To turn on built-in flashlight, slide button up on the side of the unit.



**Safety Technology
International**

2306 Airport Road
Waterford, Michigan
48327, USA

Tel: 248-673-9898
Fax: 248-673-1246
info@sti-usa.com
www.sti-usa.com

Taylor House
34 Sherwood Road
Bromsgrove, Worcestershire
B60 3DR, England

Tel: +44 (0)1527 520 999
Fax: +44 (0)1527 501 999
info@sti-emea.com
www.sti-emea.com