

Straight Blade Devices  
 15A, 125V, 2 Pole, 3 Wire Grounding  
 Insulgrip Plug



**Features**

- Ribbed nylon housing is impact and chemical resistant
- VARI-SIZE adjustable cord clamp
- Fast lead assembly screws
- Beveled housing prevents snagging

**Ordering Information**

Description	Cord Diameter	UPC	Catalog Number
Black and white nylon	.230"-.720"(5.8-18.3)	783585173009	HBL5266C

**Listings**

UL Listed to UL498 File E1706  
 CSA Certified to C22.2 No. 42 File 280  
 Fed. Spec. W-C596G  
 NEMA® WD-6 Compliant

**Specifications**

Housing/Cord Clamp	Nylon
Blade Holder	Nylon
Terminal Retainer	Clear Polycarbonate
Blades	.060 in. (1.5) Brass
Terminal Screws	#8-32 Brass , multiple drive
Terminal Clamp	Nickel plated steel
Assembly Screws	Nickel plated steel

**Performance**

**Electrical**


Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum

**Mechanical**


Terminal Accommodation	#18-10 AWG. Standed copper wire only
Terminal Identification	Terminals identified in accordance with UL 498 and CSA

**Environmental**


Flammability	UL 94 HB or better
IP Suitability	IP20
Operating Temperatures	Maximum continuous 75°C; minimum -40°C (w/o impact)




AGENCY LISTING  
 PER TABLE



ALL SCREWS ARE  
 COMBINATION  
 ROBERTSON/PHILLIPS/  
 SLOTTED HEAD



INTEGRAL VARISIZE  
 INSERT



CATALOG NUMBER  
 (HBL5266CM2 &  
 HBL5266EBK NOT  
 MARKED)

Ø 1.527 ±.015  
 [ 38.74 ±0.38mm ]

**Accessories**

Weatherproof Boot	HBL6017
-------------------	---------

**Resources**

Customer Use Drawing  
 eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

