source images

670EP

Product no.: 670EP

Tip cutter – straight short relieved head

- Suitable for cutting SMD and micro-package contacts.
- High-precision tip cutter
- For connections of SMD micro-packages up to 0.25 mm / .010 inch, also for pitches smaller than 1/20".

The Perfect Cut - Strong, sharp and precise, every time

The Weller Erem Series 600 Micro is a range of miniature precision cutters that offers a wide variety of head shapes for access in difficult to reach areas. These micro cutters are suitable for SMD and leads (670EP, 670EPF). The cutters are made from high grade tool steel with cutting edges hardened to 63-65HRc. The precision cutters have a nonreflecting surface, are ESD safe and resharpenable.

Type	Type of Cut	Cutting Capacity
Series 600 Micro & 2600		mm 0,03 0,1 0,2 0,3 0,4 0,5 0,6 0,7 0,8 0,9 1,0 1,1 1,2 1,3 1,4 1,5 1,6 1,7 1,8 1,9 2,0 Inch .0001 .003 .007 .011 .015 .019 .023 .027 .031 .035 .039 .043 .047 .051 .055 .059 .062 .066 .070 .074 .078
	612N 2612N	Semi Flush
	622N 2622N	Flush
	622TX	Flush / Carbide
	632N 2632N	Super Full Flush
	622NA	Flush
	622NB 2622NB	Flush
	676E	Flush
	776E	Super Full Flush
	632NCF	Super Full Flush — only for soft materials: silicone, rubber...
	670E	Flush
	670EP	Flush
	670EPF	Flush — for micro pitches under 0,5 mm



Swiss Made

PRECISION TOOLS

Technical Data

Length mm	110
Length of cutting edges mm	3.6
Head width mm	9
Head thickness mm	6
Head length mm	18
Max. cutting capability – hard wire mm	---
Weight in oz	1.693
Length of cutting edges Inches	0.142
Head width Inches	0.354
Head thickness Inches	0.236
Head length Inches	0.709
ESD-safe	on
Cut	Flush
Max. cutting capability – medium hardness mm	Ø 0,5
Max. cutting capability – copper wire mm	Ø 0,6
Length inches	4.331
Weight in g	48
Erem applications	Microelectronic

Weller Tools GmbH
Carl-Benz-Straße 2
74354 Besigheim
Germany

Phone: +49 (0) 7143 / 580-0
Fax.: +49 (0) 7143 / 580-108
Email: info@weller-tools.com
Web: www.weller-tools.com

CONTACT US