

DMS MANUELL 0,5-1,7**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



If you demand effective and exact work, it is essential to use the precise torque. This also guarantees high repetition accuracy.

This is the perfect job for the new Weidmüller torque screwdriver with the ergonomic grip and the unique interchangeable bit system.

- Compact and especially light design
- Torque set with special tool (supplied); an unintended, incorrect setting is ruled out.
- Ergonomic handle sizes matched to the torque range.
- Tools subjected to routine testing and provided with an ID number; 100% quality control with verification and product reference.
- Clicking sound upon reaching the set torque, clearly audible and noticeable, no unnecessary tightening.
- Interchangeable blades made from high-quality wear-resistant tool steel.
- All tools fulfil the accuracy requirements of: EN ISO 6798, BS EN 26789, ASME B107.14M
- Trigger accuracy +/- 6% of the set scale value.

General ordering data

Type	DMS MANUELL 0,5-1,7
Order No.	9918370000
Version	Tools, Torque screwdriver
GTIN (EAN)	4032248388332
Qty.	1 pc(s).

DMS MANUELL 0,5-1,7**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Width	200 mm	Width (inches)	7.874 inch
Weight	191 g	Net weight	166.1 g

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Classifications

ETIM 6.0	EC000149	ETIM 7.0	EC000149
eClass 9.0	21-04-04-07	eClass 9.1	21-04-04-90
eClass 10.0	21-04-50-03	UNSPSC	27-11-17-01

Approvals

Approvals

**Downloads**

Brochure/Catalogue [CAT 3 HDC 17/18 EN](#)
[CAT 6 TOOLS 15/16 EN](#)
[CAT 5 ENCL 17/18 EN](#)