



Premium Multimeter Test Probe Kit

Durable nylon carry case containing one red and one black soft grip premium test probe leads and two nickel plated steel alligator clips, complete with one red and one black PVC insulator.

Constructed with ultra-flex 18 AWG silicone jacketed wire and over-molded, shrouded, right angle safety 4mm banana plugs.

Probes feature snap-on safety tips for extended category III voltage ratings.

Compatible with all major Digital Multimeter brand instruments fitted with standard 4mm sockets

Nickel plated steel alligator clips attach to the standard probe tips to facilitate convenient hand-free connections.

The durable nylon carry case protects the kit from damage, tangles and snagging.

|--|

BU-P5519A	Premium Test Probe Set
Cable	Silicone Insulated 18 AWG
Current Rating	10A
Safety Category	CATIII 1000V (with safety tips)
Length	1.2 Metres
Approvals	C € RoHS Compliant

BU-60PR2 BU-62	Probe Tip Alligator Clips Red & Black PVC Insulators
Current Rating	10A
Clip Material	Nickel Plated Steel
Approvals	RoHS Compliant

Toll Free: 800.955.2626 Phone: 330.780.2525

Fax: 330.780.2524