



PRODUCT-DETAILS

TBEF0375-75

16MM GALV. STEEL CONDUIT 75M



General Information

Extended Product Type	TBEF0375-75
Product ID	7TCD012500R0440
EAN	5414363076476
Catalog Description	16MM GALV. STEEL CONDUIT 75M
Long Description	Flexible Metrallic Conduit, Size 3/8 Inch/16mm, Minimum Bend Radius 50mm, Galvanised Steel Core with PVC Jacket, Length 75 Meters

Ordering

EAN	5414363076476
-----	---------------

Dimensions

Product Net Depth / Length	75 m
Product Net Weight	64 lb 29.025 kg

Container Information

Package Level 2 Units	1 reel
Package Level 2 Width	19.9 in 505 mm

Package Level 2 Height	9.8 in 249 mm
Package Level 2 Depth / Length	20.7 in 526 mm

Additional Information

Application	Standard Multi-purpose Conduit
Brand / Label	T&B Liquidtight Fittings
Color	Black
Inside Diameter	12.5 mm
Material	Galvanized Steel with PVC Jacket
Nominal Size	16 mm
Number of Batteries	0
Outside Diameter	17.8 mm
Product Name	T&B LIQUIDTIGHT FITTINGS
Product Type	Flexible Conduit - Steel Core
Radius	50 mm
Special Functions	Flexible, Vde Approved, For Heavy-duty Use
UPC	786210521442

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TBEF0375-75
Instructions and Manuals	TBEF0375-75

Classifications

ETIM 6	EC001179 - Protective metallic hose
ETIM 7	EC001179 - Protective metallic hose
UNSPSC	39131706
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5535 >> Electrical conduit

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Liquidtight Fittings

—