



PRODUCT-DETAILS

TBEF0750-50G

25MM GALV. STEEL CONDUIT 50M GREY

General Information

Extended Product Type	TBEF0750-50G
Product ID	7TCD012500R0451
EAN	5414363126935
Catalog Description	25MM GALV. STEEL CONDUIT 50M GREY
Long Description	25MM Galvanized Steel Conduit 50M Grey

Ordering

EAN	5414363126935
-----	---------------

Dimensions

Product Net Depth / Length	50 m
Product Net Weight	82.22 lb 37.288 kg

Container Information

Package Level 2 Units	1 reel
Package Level 2 Width	29.1 in 739 mm
Package Level 2 Height	6.7 in

	170 mm
Package Level 2 Depth / Length	29.1 in 739 mm

Additional Information

Application	Standard Multi-purpose Conduit
Brand / Label	T&B Liquidtight Fittings
Color	Grey
Inside Diameter	21 mm
Material	Galvanized Steel with PVC Jacket
Nominal Size	25 mm
Number of Batteries	0
Outside Diameter	26.4 mm
Product Name	T&B LIQUIDTIGHT FITTINGS
Product Type	Flexible Conduit - Steel Core
Radius	90 mm
Special Functions	Flexible, Vde Approved, For Heavy-duty Use
UPC	786210557687

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TBEF0750-50G
Instructions and Manuals	TBEF0750-50G

Classifications

ETIM 6	EC001179 - Protective metallic hose
ETIM 7	EC001179 - Protective metallic hose
UNSPSC	39131706
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5535 >> Electrical conduit

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Liquidtight Fittings