



Known as LOCTITE E32 A/B

# Features and Benefits



## LOCTITE EA E32 A&B



☐ **Add to comparison**

Grey, 2-part, toughened, high shear and peel strength, structural epoxy adhesive which has remarkable resistance to both static and dynamic loading  
LOCTITE® EA E32 is a grey (when mixed), 2-part, toughened, high shear and peel strength, structural epoxy adhesive which has remarkable resistance to both static and dynamic loading. E32 has been selected for many industrial assemblies where structural integrity is required. Accurately metered and mixed material can be applied direct to the workpiece by using E32 in the 'EDS' cartridge pack.

- **Overnight cure provides plenty of time for complex product assembly**

# LOCTITE EA E32 A&B

- Applications extending back over 20 years confirm its excellent environmental durability
- Bonds to a wide variety of materials including metals, composites, ceramics and wood
- Accurately metered and mixed material can be applied direct to the workpiece

## Documents and Downloads

[Search for TDS in another language](#)[Search for SDS in another language](#)

## Technical Information

Color

Grey

Fixture Time

72 hr.

Fixture Time Temperature

23 °C

Mix Ratio

1:1 (by volume)

Shear Strength

26 N/mm<sup>2</sup>

Technology

Epoxy

# LOCTITE EA E32 A&B

Viscosity (#7sp/20/rpm)

80000 mPa.s (cP) Brookfield

Work Life Time

24 hr.