

Category 6 24 Port Patch Panel (SF24C2)



POE+ Compliant

Category 6 vertical patch panel (SF24C2)

TUK's latest Category 6 vertical patch panel is a high performance, stylish UTP patch panel which is excellent value for money and is ideal for installing into 19" cabinets, racks and frames. (Upgraded replacement for SF24C)

Features

- Improved version now easily performs to Category 6 standard (permanent link)
- Robust and high quality metal construction
- Supplied with an easy to remove cable management bar
- Fitted with colour coded labels and numbered ports for easy wiring. Suitable for 568A or 568B wiring.
- Accommodates LSA & 110 type termination tools

Specifications

- Weight: 658 g
- Dimensions: 483 x 390 x 45 (W x D x H)
- Colour: Black with white labelling
- Supplied with cable retention clips, caged nut set and cable ties.
- IDC contact –1.27 µm/50 µ" gold plating over 2.54 µm/60 µ" nickel over phosphor bronze
- Panel Frame – Carbon steel, powder coated black.

Packaging: Product supplied pre-assembled in individual carton then in cartons of 10

EAN: 5055386508300

Commodity code: 85177090