

3388 Fox & Hound™ Hotwire

Trace Live 120/220VAC Power Lines (250VAC max)

Features:

- Locate wires through Drywall, Plaster, Wood, Cement, etc., including buried wires up to 6"
- Trace wires up to 1000 feet for powered or unpowered common wires including telephone and cable TV wires, LAN cables, security system wires, invisible fences, landscape lighting, etc.
- Includes the versatile Fox HotWire Tone Generator (Toner) and the high performance Hound HotWire Inductive Amplifier (Probe)
- Powered by a 9V battery for Low Voltage tracing or it can be powered by the High Voltage line it is toning
- Generates multiple tones (Pulse or Warble)
- Visual and audible continuity test
- Exclusive TrueTrace function provides positive identification of non-energized wires being traced
- Lightweight Probe features a thumbwheel Sensitivity control and Signal Strength indicator LED
- Built-in LED headlights to illuminate dark areas and reduce fluorescent light noise
- Bandpass filter to suppress unwanted frequencies
- Earphone jack for noisy or quiet work areas
- The HotWire's RF signal can be sensed through both building materials and most metal conduit
- Includes Test Leads (24" and 60"), flat blades, pointed probes, alligator clips, (2) 9V batteries (not included), and hard carrying case
- Designed to meet CATII 250V
- 1 Year Warranty

Specifications

| Hotwire Fox | |
|--------------------------|--|
| Operating Frequency (RF) | 400kHz to 500kHz |
| Operating Frequency (AF) | 800Hz to 2400Hz |
| Output Voltage (RF) | adjustable 5vpp to 30vpp (open circuit) |
| Output Voltage (AF) | Fixed 10vpp (open circuit) |
| Tracer Tone | Warble or Pulsed, High or Low Pitch |
| Max. AC/DC Live Voltage | 250V |
| Continuity Test | Up to 5,000 ohms with audible beeper |
| AC Voltage Test | 30VAC to 250VAC |
| DC Voltage Test | Positive applied to red test lead 40VDC to 250VDC |
| Dimensions/Weight | 3.5 x 4.5 x 1.5" (89 x 114 x 38mm) / 7 oz (198g) |
| Hotwire Hound | |
| Operating Frequency (RF) | 400kHz to 500kHz |
| Signal Indicators | Speaker outputs Tracer signal and LED indicates signal strength |
| Earphone Jack | Accepts 1/8" mono or stereo earphone plug (mutes speaker) |
| Headlights | 2 High Brightness White LEDs |
| Speaker | 1.5" Mylar cone with Alnico magnet |
| Dimensions | 1-7/8" (48mm) dia at speaker; 1-3/8" (35mm) dia at body; 7.5" (191mm) long |
| Weight | 9 oz (255g) |



Ordering Information:

3388 Fox & Hound™ Hotwire