

PRO-SIGNAL

SAFETY WARNINGS


Keep the headphone clean and dust free or the sound quality may be reduced.


Do not subject the headphones to impact or excessive vibration.


Do not allow water or other liquids to enter the headphones.


Be aware that wearing for long periods and at high volume may cause fatigue and hearing damage.

OPERATION

Turn on/off: Press and hold  for 3 seconds. The blue & red LED will flash. From your source device search for wireless device "PSG3412-M292" to connect. No pass required. Use "0000" if your device demands one. The blue LED flashes slowly when connected.

Play/pause: Short press  to play/pause music.

Call answer : Short press  button again in standby or during music-play mode.

Call end: Short press  button.

Call redial last number: Press the  button twice in standby or music-play mode.

Volume: Long press + or - to increase or reduce the volume.

Next/last song: Short press + or - to play next or last song.

Noise Cancel Function: Short press **M** button to turn ANC mode on or off. When on, green LED is lit.

Charging: Insert the charge cable to the micro USB slot, the red LED will light. It will extinguish when fully charged.

External Audio Input: In power on mode, plugging in an external source automatically switches to AUX mode.

SPECIFICATIONS

USB charge: DC 5V

Wireless frequency: 2.401-2.480GHz

Wireless distance: ≤10 meters

Frequency: 20Hz-20KHz

Output power: 30mW

SNR: ≥75dB

Charging time: <2.5 hours

Active noise reduction: 18-25dB



**WIRELESS NOISE CANCELLING
HEADPHONES
PSG3412-M292**

**MADE IN CHINA
PR2 9PP**

