

Cordless hot air tool - Professional Line

mobile heat MH3 5,5 Ah

UK including rechargeable 5.5Ah battery and charger
EAN 4007841 068332



Function description

Mobile. Fast. Precise. mobile heat MH3, the 18 V cordless hot air tool with 2 temperature settings (300°C/500°C). Heats up to 300°C in a maximum of 5 seconds. High-performance, with an airflow rate of up to 200 l/min. The security lock button and LED illumination on the base of the tool ensure safe working. Compatible with all push-on standard nozzles from STEINEL. Including case (upon request, with CAS rechargeable battery and charger)

Technical specifications

Temperature	300 – 500 °C
Airflow rate	200 l/min
Motor, type	Brush motor
Function, life expectancy, motor	500 h
Temperature setting	2-stage
Temperature display	LED segment display
Power supply, detail	Rechargeable lithium-ion battery
Heating element	Ceramic heating element
Loc function	No
Residual heat indicator	No
Function, hanger	Yes

Replaceable heating element	No
Thermal cut-out	Yes
Thermostat	No
Dimensions (L x W x H)	225 x 72 x 204 mm
Rechargeable battery voltage	18 V
Mains power supply	18 V
Model	Case
PU1, net weight	0,68 kg
Manufacturer's Warranty	1 year
PU1, EAN	4007841068332

Accessories

EAN 4007841 068257 Spare CAS battery 18V LiHD