

REV	DESCRIPTION	SIGNATURE	DATE
A1	ORIGIN	Flynn	2020.09.09

TABLE A




TABLE A

P/N	Customer P/N:	Length (mm)
AOCHDMI-007-5		7500+/-150
AOCHDMI-010		10000+/-200
AOCHDMI-015		15000+/-250
AOCHDMI-020		20000+/-300
AOCHDMI-030		30000+/-400

11	QR Code	1	PCS
10	Screw	4	PCS
9	Metal	2	PCS
8	SR	2	PCS
7	HDMI A plug Bottom Shell(Display)	1	PCS
6	HDMI A plug Bottom Shell(Source)	1	PCS
5	HDMI A plug Up Shell	2	PCS
4	HDMI A PCBA (Display)	1	PCS
3	HDMI A PCBA (Source)	1	PCS
2	HDMI A Pin Male Gold-plating	2	PCS
1	HDMI AOC (4 Fiber+7 Copper) Black PVC OD:4.5MM	TABLE A	mm
ITEM	SPECIFICATIONS	Q' TY	UNIT

	TOLERANCES UNLESS OTHERWISE STATED
X.	= ± 1
X.X	= ± 0.2
X.XX	= ± 0.1
	TOOLING
X.	DECIMALS ANGLES
X.X	±0.3 ± 1°
X.XX	±0.2 ± 0.5°
X.XXX	±0.1 ± 0.5°

CUSTOMER P/N:			
TYPE:HDMI 2.1 Active Optical Cable			
DRAW: Flynn	PAPT NO:		
CKD:	CUSTOMER:	UNIT:mm	
APP:	DWG NO:	REV:1	
SHELL:1/1		DATE:2020.09.09	