



REF. ID	REF. NO.	SIGNAL	WIRE COLOR	GAUGE	CONNECTOR TYPE	CABLE LENGTH
P1	1	+3.3V	ORANGE	20	P1-1 P4-2 P20-1 P4202K11D+ P4202K11D P4202K11D or EQUIV.	500±15mm
	2	+3.3V	ORANGE	20		
	3	COM	BLACK	20		
	4	+5V	RED	20		
P2	1	+5V	RED	20	P2-1 P4-2 P20-1 P4202K3B+ P4202K4B or EQUIV.	430±15mm
	2	+3.3V	ORANGE	20		
	3	COM	BLACK	18		
	4	COM	BLACK	18		
	5	+12V	YEL/BLACK	18		
	6	+12V	YEL/BLACK	18		
	7	+12V	YEL/BLACK	18		
	8	+12V	YEL/BLACK	18		
	9	+12V	YEL/BLACK	18		
	10	+12V	YEL/BLACK	18		
	11	+12V	YEL/BLACK	18		
	12	+12V	YEL/BLACK	18		
P3	1	+12V	YELLOW	18	P3-1 P4-2 P20-1 P4202BK5 P4202BK5 or EQUIV.	430±15mm
	2	+12V	YELLOW	18		
	3	+12V	YELLOW	18		
	4	COM	BLACK	18		
P4	1	+5V	RED	20	P4-1 P4-2 P20-1 P4202K3B+ P4202K4B or EQUIV.	430±15mm
	2	+5V	RED	20		
	3	COM	BLACK	18		
	4	COM	BLACK	18		
P5	1	+5V	RED	20	P5-1 P4-2 P20-1 P4202K3B+ P4202K4B or EQUIV.	410±15mm
	2	+5V	RED	20		
	3	COM	BLACK	20		
	4	COM	BLACK	20		
	5	+12V	YELLOW	20		
P6	1	+5V	RED	20	P6-1 P4-2 P20-1 P4202K3B+ P4202K4B or EQUIV.	155±10mm
	2	+5V	RED	20		
	3	COM	BLACK	20		
	4	COM	BLACK	20		
P7	1	+5V	RED	20	P7-1 P4-2 P20-1 P4202K3B+ P4202K4B or EQUIV.	155±10mm
	2	+5V	RED	20		
	3	COM	BLACK	20		
	4	COM	BLACK	20		
P8	1	+5V	RED	20	P8-1 P4-2 P20-1 P4202K3B+ P4202K4B or EQUIV.	155±10mm
	2	+5V	RED	20		
	3	COM	BLACK	20		
	4	COM	BLACK	20		
P9	1	+5V	RED	20	P9-1 P4-2 P20-1 P4202K3B+ P4202K4B or EQUIV.	155±10mm
	2	+5V	RED	20		
	3	COM	BLACK	20		
	4	COM	BLACK	20		
P10	1	+5V	RED	20	P10-1 P4-2 P20-1 P4202K3B+ P4202K4B or EQUIV.	155±10mm
	2	+5V	RED	20		
	3	COM	BLACK	20		
	4	COM	BLACK	20		

NOTE:
1. ALL THE LENGTH OF OUTPUT WIRES EXCLUDE HOUSING.

MODEL NO.: FSP400-60AGB(S0330002)

R&D(2)

PE

DRAWN

樂家龍

DATE

Jun.16.2020

TITLE: ASSY

SHEET: 1 OF 1

REV:01

SPI P/N.: FSP400AGB-B204

P/N.: 9PA400D101

UNIT:mm