



NEW SG-Y10 - YELLOW SAFETY GLASSES
WITH INDOOR/OUTDOOR LENSES

- Super tough nylon-polymer frame with 8-base curvature
- Toughened polycarbonate lenses
- Indoor & outdoor mirror lens coating
- With 99% UV A/B/C protection (EN170)
- Anti-scratch & anti-fog lens coatings
- Flexible PC & TPR co-injected side arms
- Rubberised TPR inner arm grips
- Comfortable TPR non-slip nose grip with reinforced bridge
- Side TPR temple shields with ventilation
- Micro-fibre drawstring storage bag included



CERTIFICATIONS

CE - EN166
USA - ANSI Z87.1
AUS/NZ - AS/NZS 1337.1

WEIGHT 33.5g



Lens Filters: 2 (UV EN170) 1.4 (indoor & outdoor)
Optical Class: 1 (high optical quality)
Mechanical risk - Low energy impact - F
High speed particles at extreme temperatures - T

